







SPECIFICATIONS :

MATERIAL:

1. HOUSING MATERIAL: GLASS FILLED PA9T(UL94V-0)
2. CONTACT MATERIAL: PHOSPHOR BRONZE T=0.3MM.
3. PLATING: GOLD PLATING $Fu''-50u''$ OVER NICKEL.

ELECTRICAL:

1. VOLTAGE RATING: 125Vac RMS .
2. CURRENT RATING: 1.5AMP .
3. CONTACT RESISTANCE: $30m\Omega$ MAX .
4. INSULATION RESISTANCE: $500M\Omega$ MIN @ 500Vdc .
5. DIELECTRIC WITHSTANDING VOLTAGE: 1000Vac RMS 50Hz 1MIN.

MECHANICAL:

1. DURRABILITY : 750 CYCLES MIN.
2. INSETION FORCE: 2.2Kgf .MAX
3. RETENTION STRENGTH : 7.7Kgf MIN BETWEEN JACK AND PLUG

ENVIRONMENTAL:

1. STORAGE TEMPRATURE : -40° C TO 85° C.
2. OPERATION TEMPRATURE : -40° C TO 85° C.

TOLERANCE TABLE	
.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO., LTD					
CHECKED:	DATE:	TITLE: RJ45-8P/8C 56L 弯插 带屏蔽 无灯无弹 小柱					
DRAWN: YKX	DATE: 2026-07-14	PART. NO.	R-RJ45R08P-BT03				
		UNIT	mm	SCALE	free		
		FILE NO.	Ckmtw-RJ45-0573		REV.	A	KC01