








技术指标:

1. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. 额定电压: 150V AC, DC.
3. 耐压: 500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$ (Initial) per contact, $\leq 40\text{m}\Omega$ Change allowed.
5. 绝缘电阻: $\geq 500\text{M}\Omega$.
6. 额定电流: 1A AC, DC.

材质:

1. 塑胶: PA66 白色



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

型号	CKT	A	B	C
C-DF1.25-2-M5P12	2*5	10.50	5.00	7.86
C-DF1.25-2-M6P12	2*6	11.75	6.25	9.11
C-DF1.25-2-M7P12	2*7	13.00	7.50	10.36
C-DF1.25-2-M8P12	2*8	14.25	8.75	11.61
C-DF1.25-2-M9P12	2*9	15.50	10.00	12.86
C-DF1.25-2-M10P12	2*10	16.75	11.25	14.11
C-DF1.25-2-M11P12	2*11	18.00	12.50	15.36
C-DF1.25-2-M12P12	2*12	19.25	13.75	16.61
C-DF1.25-2-M14P12	2*14	21.75	16.25	19.11
C-DF1.25-2-M15P12	2*15	23.00	17.50	20.36
C-DF1.25-2-M16P12	2*16	24.25	18.75	21.61
C-DF1.25-2-M17P12	2*17	25.50	20.00	22.86
C-DF1.25-2-M18P12	2*18	26.75	21.25	24.11
C-DF1.25-2-M19P12	2*19	28.00	22.50	25.36
C-DF1.25-2-M20P12	2*20	29.25	23.75	26.61
C-DF1.25-2-M21P12	2*21	30.50	25.00	27.86
C-DF1.25-2-M22P12	2*22	31.75	26.25	29.11
C-DF1.25-2-M23P12	2*23	33.00	27.50	30.36
C-DF1.25-2-M24P12	2*24	34.25	28.75	31.61
C-DF1.25-2-M25P12	2*25	35.50	30.00	32.86

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.*±5°	PART NO.	TITLE:		
.XX±0.25	X.X°±1°	C-DF1.25-2-MNP12	1.25 Pitch A型(DF13)双排公头胶壳		
.XXX±0.15		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1