



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Technical Index

- 1.Temperature range:−25°C~+85°C.
- 2.Rated voltage:150V DC/AC.
- 3.Rated current:1.0A.
- 4.Contact resistance:
 - ≤20mΩ(Initial) per contact,
 - ≤40mΩ Change allowed.
- 5.Dielectricwithstanding voltage:500V AC/minute.
- 6.Insulation resistance:≥500MΩ.
- 7.Apply to gauge:AWG#26~AWG#30.(O.D 1.0mm Max)



序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	X.*±5°	PART NO. B-DF1.25-2DP2	TITLE: 1.25 Pitch A型(DF13) 双排公头端子	
.XX±0.25	X.X°±1°		MANUFACTURE DWG	
.XXX±0.15				
UNITS	mm	DESIGN:	Ethan	
MATERILA	---	CHED:	Olvia	
FINISH	---	APPD:	Ava	
				SCALE N:A
				SHEET 1/1