



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Part No	Pin	A	B	C	D	E
AFPC0501-4PH2.0	4	1.50	2.52	5.45	5.25	0.17
AFPC0501-5PH2.0	5	2.00	3.02	5.95	5.75	
AFPC0501-6PH2.0	6	2.50	3.52	6.45	6.25	
AFPC0501-7PH2.0	7	3.00	4.02	6.95	6.75	
AFPC0501-8PH2.0	8	3.50	4.52	7.45	7.25	
AFPC0501-9PH2.0	9	4.00	5.02	7.95	7.75	
AFPC0501-10PH2.0	10	4.50	5.52	8.45	8.25	
AFPC0501-11PH2.0	11	5.00	6.02	8.95	8.75	
AFPC0501-12PH2.0	12	5.50	6.52	9.45	9.25	
AFPC0501-13PH2.0	13	6.00	7.02	9.95	9.75	
AFPC0501-14PH2.0	14	6.50	7.52	10.45	10.25	
AFPC0501-15PH2.0	15	7.00	8.02	10.95	10.75	
AFPC0501-16PH2.0	16	7.50	8.52	11.45	11.25	
AFPC0501-17PH2.0	17	8.00	9.02	11.95	11.75	
AFPC0501-18PH2.0	18	8.50	9.52	12.45	12.25	
AFPC0501-19PH2.0	19	9.00	10.02	12.95	12.75	
AFPC0501-20PH2.0	20	9.50	10.52	13.45	13.25	0.18
AFPC0501-21PH2.0	21	10.00	11.02	13.95	13.75	
AFPC0501-22PH2.0	22	10.50	11.52	14.45	14.25	
AFPC0501-23PH2.0	23	11.00	12.02	14.95	14.75	
AFPC0501-24PH2.0	24	11.50	12.52	15.45	15.25	
AFPC0501-25PH2.0	25	12.00	13.02	15.95	15.75	
AFPC0501-26PH2.0	26	12.50	13.52	16.45	16.25	
AFPC0501-27PH2.0	27	13.00	14.02	16.95	16.75	
AFPC0501-28PH2.0	28	13.50	14.52	17.45	17.25	
AFPC0501-29PH2.0	29	14.00	15.02	17.95	17.75	
AFPC0501-30PH2.0	30	14.50	15.52	18.45	18.25	
AFPC0501-31PH2.0	31	15.00	16.02	18.95	18.75	
AFPC0501-32PH2.0	32	15.50	16.52	19.45	19.25	
AFPC0501-33PH2.0	33	16.00	17.02	19.95	19.75	
AFPC0501-34PH2.0	34	16.50	17.52	20.45	20.25	
AFPC0501-35PH2.0	35	17.00	18.02	20.95	20.75	
AFPC0501-36PH2.0	36	17.50	18.52	21.45	21.25	
AFPC0501-37PH2.0	37	18.00	19.02	21.95	21.75	
AFPC0501-38PH2.0	38	18.50	19.52	22.45	22.25	
AFPC0501-39PH2.0	39	19.00	20.02	22.95	22.75	

技术指标:


1. 额定电流: 0.5A
2. 温度范围: -40~85℃
3. 额定电压: 50V, AC/DC (等效)
4. 接触电阻: $\leq 0.03\Omega$
5. 绝缘电阻: $\geq 500M\Omega$




SECTION A-A




序号	品名	材质
1	端子	磷青铜/表面镀锡
2	焊片	磷青铜/表面镀锡
3	基座	LCP UL94V-0 本色
4	锁条	LCP UL94V-0 黑色






TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.15	±1°	PART NO.	TITLE:		
X.X±0.10		AFPC0501-NPH2.0	0.5-G前插后压(H:2.0)		
X.XX±0.05		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/2

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




技术指标:


1. 额定电流: 0.5A
2. 温度范围: -40~85℃
3. 额定电压: 50V, AC/DC (等效)
4. 接触电阻: $\leq 0.03\Omega$
5. 绝缘电阻: $\geq 500M\Omega$



Part No	Pin	A	B	C	D	E
AFPC0501-40PH2.0	40	19.50	20.52	23.45	23.25	0.18
AFPC0501-41PH2.0	41	20.00	21.02	23.95	23.75	
AFPC0501-42PH2.0	42	20.50	21.52	24.45	24.25	
AFPC0501-43PH2.0	43	21.00	22.02	24.95	24.75	
AFPC0501-44PH2.0	44	21.50	22.52	25.45	25.25	
AFPC0501-45PH2.0	45	22.00	23.02	25.95	25.75	
AFPC0501-46PH2.0	46	22.50	23.52	26.45	26.25	
AFPC0501-47PH2.0	47	23.00	24.02	26.95	26.75	
AFPC0501-48PH2.0	48	23.50	24.52	27.45	27.25	
AFPC0501-49PH2.0	49	24.00	25.02	27.95	27.75	
AFPC0501-50PH2.0	50	24.50	25.52	28.45	28.25	0.20
AFPC0501-51PH2.0	51	25.00	26.02	28.95	28.75	
AFPC0501-52PH2.0	52	25.50	26.52	29.45	29.25	
AFPC0501-53PH2.0	53	26.00	27.02	29.95	29.75	
AFPC0501-54PH2.0	54	26.50	27.52	30.45	30.25	
AFPC0501-55PH2.0	55	27.00	28.02	30.95	30.75	
AFPC0501-56PH2.0	56	27.50	28.52	31.45	31.25	
AFPC0501-57PH2.0	57	28.00	29.02	31.95	31.75	
AFPC0501-58PH2.0	58	28.50	29.52	32.45	32.25	
AFPC0501-59PH2.0	59	29.00	30.02	32.95	32.75	
AFPC0501-60PH2.0	60	29.50	30.52	33.45	33.25	



序号	品名	材质
1	端子	磷青铜/表面镀锡
2	焊片	磷青铜/表面镀锡
3	基座	LCP UL94V-0 本色
4	锁条	LCP UL94V-0 黑色

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X. ± 0.15	$\pm 1^\circ$	PART NO.	TITLE:		
X.X ± 0.10		AFPC0501-NPH2.0	0.5-G前插后压(H:2.0)		
X.XX ± 0.05		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	2/2