





ABIDE BY ROHS




| ITEM | H   |   |
|------|-----|---|
| 01   | 7.3 | √ |
| 02   | 7.5 |   |



P. C. B. Layout



- Remarks:
1. Rated current, Voltage: DC 12V 50mA
  2. Contact resistance:  $\leq 50\text{m}\Omega$
  3. Insulation resistance:  $\geq 100\text{M}\Omega$
  4. The intensity of operations:  $260 \pm 50\text{gf}$
  5. Life requirements: 100000 times
  6. Withstand voltage: AC250V 1 minute
  7. All materials comply with RoHS standards



- Remarks:
1. Braiding process, can not be caused by carrying half crushed;
  2. Pay attention to the direction of the tape, with a clockwise direction out of the carrier tape, with a hole in the top or right

|     |           |          |     |               |
|-----|-----------|----------|-----|---------------|
| 5   | Button    | PPA      | 1   | Yellow        |
| 4   | Cover     | Q195     | 1   | Cu-Sn Plating |
| 3   | Shrapnel  | SUS      | 1   | Ag Plating    |
| 2   | Housing   | PPA      | 1   | Black         |
| 1   | Terminal  | Brass    | 4   | Ag Plating    |
| NO. | PART NAME | MATERIAL | QTY | FINISHING     |

| 单位<br>UNIT      | mm | 一般公差<br>TOLERANCE ARE |            | 浙江恩盛电子有限公司<br>Zhejiang Ensheng Electronics Co., Ltd. |                         |
|-----------------|----|-----------------------|------------|------------------------------------------------------|-------------------------|
| 绘图<br>DRAWN     |    | $X \leq 1$            | $\pm 0.05$ | 产品名称<br>TITLE                                        | 轻触开关                    |
| 设计<br>DESIGN    |    | $1 \leq X \leq 5$     | $\pm 0.10$ |                                                      |                         |
| 审核<br>CHECKED   |    | $5 \leq X \leq 10$    | $\pm 0.15$ |                                                      |                         |
| 校准化<br>STANDARD |    | $X > 10$              | $\pm 0.25$ | 产品型号<br>MODEL                                        | 12*12方头贴片               |
| 批准<br>APPROVALS |    | 重量<br>WT.             |            | 产品编码<br>PART NO                                      | ES1204-10XX-73X-26-B-YF |
|                 |    | 产地<br>PRODUCTION      |            | 视角<br>PROJ                                           | 比例<br>SCALE             |
|                 |    |                       |            |                                                      | 页码<br>SHEET             |
|                 |    |                       |            |                                                      | 1 OF 1                  |

| ECN NO. | REV | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |
|---------|-----|-------|--------------|---------|--------|--------|
| 5       |     |       | NEW          |         |        |        |