



HSF



RoHS






SPECIFICATIONS

- Voltage rating: 250V AC/DC
- Current rating: 5A, AC, DC
- Withstanding Voltage: 1500V AC/minute
- Insulation resistance: 1000M Ω min
- Temperature range: -25°C~+85°C
- Contact resistance: 20m Ω max

TERMINAL





- Part NO: AW3045R-2xNP-B

- Poles: 02-24P
- Housing Material: Nylon66 15%GF UL94V-0 Black
- Pin Material: Brass
- Contact Area Plating: Tin-Plated
- The Dimension Marked "▼" Must Be Recorded
- Without positioning posts




CIRCUIT SIZE LAYOUT

Poles	PART NO.	Dimensions (mm)	
		A	B
2	AW3045R-2*1P		6.65
4	AW3045R-2*2P	3.00	9.65
6	AW3045R-2*3P	6.00	12.65
8	AW3045R-2*4P	9.00	15.65
10	AW3045R-2*5P	12.00	18.65
12	AW3045R-2*6P	15.00	21.65
14	AW3045R-2*7P	18.00	24.65
16	AW3045R-2*8P	21.00	27.65
18	AW3045R-2*9P	24.00	30.65
20	AW3045R-2*10P	27.00	33.65
22	AW3045R-2*11P	30.00	36.65
24	AW3045R-2*12P	33.00	39.65

P. C. B. LAYOUT
08P-24PP. C. B. LAYOUT
6 CKT HEADERP. C. B. LAYOUT
4 CKT HEADERP. C. B. LAYOUT
2 CKT HEADER

Unless Otherwise specified tolerance
X. ± 0.35 X. XX: ± 0.20
X. X: ± 0.25 X. XXX: ± 0.15

SCALE: As Shown UNIT: mm
DRAW Jack Bao DATE 07/08/2017
CHECK Bob Yang DATE 07/08/2017



ANTENK ELECTRONICS CO., LTD
Http://www.antenk.com
E-mail: sales@antenk.com

TITLE: MX3.0mm 90 wafer connector without locating pegs

DRAWING NO: AW3045R-2X4P

PRODUCT NO: AW3045R-2X4P

DESCRIPTION

DATE

REV