





剖面A-A



剖面B-B



C向

技术要求:

1. 标识清晰可见, 表面不得有划痕, 裂纹, 变形, 起泡, 污损, 毛刺等明显影响使用功能和接触性能的缺陷;
2. 材料: 磷铜, 厚度0.2mm;
3. 表面处理: 镀锡;
4. 额定功率: 250V AC/DC 3A;
5. 温度范围: -25~+85℃;
6. 接触电阻: $\leq 0.02\Omega$;
7. 绝缘电阻: $\geq 500M\Omega$;
8. 耐压: 1000V AC/Min;
9. 适用线规: AWG18#~22#

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
X.:±0.5	X':0.5'	APR.	Alex	TITLE: VH3.96MM TERMINAL	
X.X:±0.1	X.X':0.1'	CHK.	Jack	DWG NO. XY-VH3.96-31	
X.XX:±0.01		DRA.	Can	PROJ.	CUSTOMER DRAWING
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A