




HSF



P. C. B LAYOUT

SPECIFICATIONS:

Current Rating:	1Amp
Insulation Resistance:	1000M ohms min
Contact Resistance:	20M ohms max
Dielectric Withstanding:	AC500V
Operating Temperature:	-65° C to +125° C
Contact Material:	Brass
Insulator Material:	PA6T, UL94V-0, Black

Ordering Code:

PHCS08	-	X	-	X	-	D	-	A-C-B	-	X	-	X	-	X
①		②		③		④		⑤		⑥		⑦		⑧

- Series No:
- No. of Contacts:
02 To 100
- Contact Plating:
G0:Gold flash S0:Selective
G1:3U" Gold S1:Selective 3u"
G2:5u" Gold S2:Selective 5u"
G3:10u" Gold S3:Selective 10u"
G4:15u" Gold S4:Selective 15u"
G5:30u" Gold S5:Selective 30u"
SN:Tin
- Connector Type:
D: Dual
- Pin Length:
A: 0300=3.00mm
C: 0500=5.00mm
B: 0180=1.80mm
Please mark the desired length in the A/C/B
- Insulator Material:
B:PA6T
C:LCP
E:PA9T
- Packing:
A:Tray
B:Bag
T:Tube
U:Tube+CAP
R:Tape&Reel
W:Tape&Reel+CAP
- Plastic High:
H1:1.6mm
H2:2.0mm
H3:2.5mm

Standard IE P/N :

PHCS08-04G0D-0230-0900-0230-BBH2


A	C	B	Unless Otherwise specified tolerance	
3.0	5.0	1.8	X. ±0.35	X. XX: ±0.20
			X. X: ±0.25	X. XXX: ±0.15
Optional			SCALE:	UNIT:
			As Shown	mm



ANTENK ELECTRONICS CO., LTD
Http://www.antenk.com
E-mail:sales@antenk.com

DRAW YG ZHONG DATE 12/07/2015

CHECK BobYang DATE 12/07/2015



TITLE: 1.27mm Pin Header Dual Row Double Plastic Straight Type

DRAWING NO: PHCS08-04G0D-0230-0900-0230-BBH2

PRODUCT NO: PHCS08-04G0D-0230-0900-0230-BBH2

REV	DESCRIPTION	DATE
	Increase packing method and material	2016/10/25