

HSF







SPECIFICATION

Current Rating:	3 Amp
Insulation Resistance:	1000M ohms min
Contact Resistance:	20M ohms max
Dielectric Withstanding:	AC500V
Operating Temperature:	-65°C to +125°C
Contact Material:	Brass
Insulator Material:	PBT,UL 94V-0 Black

Ordering Code:

PHER01 - X - X - S - A - D - B - X - X - X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No:
② No. of Contacts
01 To 40
③ Contact Plating:
G0:Gold flash S0:Selective
G1:3U" Gold S1:Selective 3u"
G2:5u" Gold S2:Selective 5u"
G3:10u" Gold S3:Selective 10u"
G4:15u" Gold S4:Selective 15u"
G5:30u" Gold S5:Selective 30u"
SN:Tin
④ Connector Type
S:Single
⑤ Pin Length:
A:0600=6.00mm
D:0120=1.20mm
B:0300=3.00mm
Please mark the desired length in the A/D/B
- ⑥ Insulator Material
A:PBT
B:PA6T
C:LCP
D:PA46
E:PA9T
⑦ Packing:
A:Tray
B:Bag
T:Tube
U:Tube+CAP
R:Tape&Reel
W:Tape&Reel+CAP
⑧ Plastic High
H1:1.70mm
H2:2.54mm
H3:2.00mm
H4:1.50mm



PCB LAYOUT

Standard IE P/N :

PHER01-03-G0-S-0584-0120-0300-A-B-H2

A	D	B	Unless Otherwise specified tolerance	
6.00	1.20	3.00	X. ±0.35 X.X: ±0.25	X.XX: ±0.20 X.XXX: ±0.15
Optional			SCALE: As Shown	UNIT: mm
			DRAW YG ZHONG	DATE 01/05/2016
			CHECK BobYang	DATE 01/05/2016
			3rd ANGLE PROJECTION	



ANTENK ELECTRONICS CO., LTD
Http://www.antenk.com
E-mail:sales@antenk.com

TITLE:

2.54mm Pin Header Single Row Angle Type standard shape

DRAWING NO: PHER01-03-G0-S-0584-0120-0300-A-B-H2

PRODUCT NO: PHER01-03-G0-S-0584-0120-0300-A-B-H2

ADD H4=1.5MM

Increase packing method and material

DESCRIPTION

DATE

REV