





NOTES:
1.CONNECTOR SURFACE CLEAN, NO RUST, OXIDE, CRACKS,
MISSING CORES, BURRS, AND OTHER MACHINERY DAMAGE.
2.HOUSING:LCP,COLOR:NATURAL.
3.CONTACTS:BRASS TIN PLATING.
4.PEG:BRASS TIN PLATING.



No. of Contacts	DIM A	DIM B	DIM C
2	2.0	7.9	4.75
3	4.0	9.9	6.75
4	6.0	11.9	8.75
5	8.0	13.9	10.75
6	10.0	15.9	12.75
7	12.0	17.9	14.75
8	14.0	19.9	16.75
9	16.0	21.9	18.75
10	18.0	23.9	20.75
11	20.0	25.9	22.75
12	22.0	27.9	24.75
13	24.0	29.9	26.75
14	26.0	31.9	28.75
15	28.0	33.9	30.75
16	30.0	35.9	32.75

东莞市高钺达电子科技有限公司					NAME(INTENDED USE) CUSTOMER DRAWING			
APPROVALS		DATE	TOLERANCES UNLESS OTHERWISE SPECIFIED		PART NO.:			
DR: 刘工		2025.05.18	X.±0.30	X.±5'	WAFX-X-T1T1-2000-A			
CHKD: 刘工		2025.05.18	.X±0.25	.X±3'	DESCRIPTION:			
APPD: 张工		2025.05.18	.XX±0.20	.XX±1'	2.0—NP立贴加盖 卷装,亮锡, LCP			
					SIZE	UNITS	SCALE	SHEET
					A4	mm	1:1	1/1

REV	ECN No.	DESCRIPTION	DATE
A	EC-25050801	RELEASE	2025-05-08

A

B

C

D

E



A

B

C

D

E



- 包装说明:
- 材料: PS白色雾透 T=0.35mm.
 - 胶盘封口胶带以实际为准.
 - 装箱盘数以实际为准.
 - 客户特殊要求按客户要求执行.

产品型号	带宽W	包装数量	装箱数量
2.0-2P 立贴	16mm	700/RELL	20R
2.0-3P~5P 立贴	24mm		14R
2.0-6P~8P 立贴	32mm		11R
2.0-9P~14P 立贴	44mm		8R
2.0-15P~16P 立贴	56mm		6R

东莞市高钺达电子科技有限公司					NAME(INTENDED USE) PACKING DRAWING				
APPROVALS		DATE	TOLERANCES UNLESS OTHERWISE SPECIFIED		PART NO.:				
DR:		2025.05.08	X.±0.30	X.±5°	DESCRIPTION: 2.0-NP 立贴包装规范				
CHKD:		2025.05.08	.X±0.25	.X±3°					
APPD:		2025.05.08	.XX±0.20	.XX±1°					
						SIZE	UNITS	SCALE	SHEET
						A4	mm	1:1	1/1