






版次	变更摘要	日期	序号	品名	材质
0	新产品发行	2019/07/20	①	HY2.0直针WTB胶芯	PA66 UL94V-0 米色 白色
			②	HY2.0直针WTB端子	铜合金/表面镀锡




TYPE 1(无K脚)



TYPE 2(打K脚)



SECTION A-A



CKT	A	B	CKT	A	B
2	2.0	6.0	12	22.0	26.0
3	4.0	8.0	13	24.0	28.0
4	6.0	10.0	14	26.0	30.0
5	8.0	12.0	15	28.0	32.0
6	10.0	14.0	16	30.0	34.0
7	12.0	16.0	17	32.0	36.0
8	14.0	18.0	18	34.0	38.0
9	16.0	20.0	19	36.0	40.0
10	18.0	22.0	20	38.0	42.0
11	20.0	24.0			


深圳市文章济美科技有限公司

品名 (TITLE)	HY2.0直针WTB	制图 (DR)	Anlan
料号 (DWG.NO)	5001-HY0020C-**-P1-00-B	校对 (CHKD)	王涛
比例 (SCALE)	1:1	审核 (APPD)	黄志明
单位 (UNITS)	mm	张数 (SHEET)	1 OF 1
尺寸 (SIZE)	A4	REV	A

技术指标 (Technical Index):

- 温度范围 (Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
- 额定电压 (Rated voltage): 200V, AC.
- 额定电流 (Rated current): 2.0A AC, DC.
- 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
- 耐压值 (Withstanding voltage): 500V AC/minute.
- 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\Omega$.
- 产品料号 (Product material No.):

5001 - HY 0020 C - ** P 1
JM CONNECTOR SERIES
PITCH: 2.0
C: 直插
ALTERNATE
PACKING: P: 袋
PIN



适用线路板 (PCB LAYOUT)



一般公差 (TOLERANCE)
X ± 0.50 XX ± 1.0
X ± 0.20 XXX ± 0.05
ANGLES $\pm 1^{\circ}$