

HSF



ROHS





SPECIFICATION

Current Rating:	3 Amp
Insulation Resistance:	1000M ohms min
Contact Resistance:	20M ohms max
Dielectric Withstanding:	AC500V
Operating Temperature:	-65°C to +125°C
Contact Material:	Brass
Insulator Material:	PBT,UL 94V-0 Black

Ordering Code:

PHER01 - X - X - S - A - D - B - X - X - X - A
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No:
② No. of Contacts
01 To 40
③ Contact Plating:
G0:Gold flash S0:Selective
G1:3U" Gold S1:Selective 3u"
G2:5u" Gold S2:Selective 5u"
G3:10u" Gold S3:Selective 10u"
G4:15u" Gold S4:Selective 15u"
G5:30u" Gold S5:Selective 30u"
SN:Tin
④ Connector Type
S:Single
⑤ Pin Length:
A:0600=6.00mm
D:0120=1.20mm
B:0300=3.00mm
Please mark the desired length in the A/D/B
- ⑥ Insulator Material
A:PBT
B:PA6T
C:LCP
D:PA46
E:PA9T
⑦ Packing:
A:Tray
B:Bag
T:Tube
U:Tube+CAP
R:Tape&Reel
W:Tape&Reel+CAP
⑧ Plastic High
H1:1.70mm
H2:2.54mm
H3:2.00mm
H4:1.50mm
⑨ Connector direction
A:standard shape




PCB LAYOUT

Standard IE P/N :

PHER01-15G0S-0600-0120-0300-ABH4A

A	D	B	Unless Otherwise specified tolerance		 ANTENK ELECTRONICS CO., LTD Http://www.antenk.com E-mail:sales@antenk.com
6.00	1.20	3.00	X. ±0.35	X.XX: ±0.20	
Optional		SCALE: As Shown	X.X: ±0.25	X.XXX: ±0.15	
DRAW YG ZHONG			DATE 01/05/2016	UNIT: mm	TITLE:
CHECK BobYang			DATE 01/05/2016		2.54mm Pin Header Single Row Angle Type standard shape
DRAWING NO:			PHER01-15G0S-0600-0120-0300-ABH4A		
PRODUCT NO:			PHER01-15G0S-0600-0120-0300-ABH4A		



3rd ANGLE PROJECTION

ADD H4=1.5MM

Increase packing method and material

REV

DESCRIPTION

DATE