


CONNECTORS

Operation: 側立式/DIP3.0-USB-SOCKETS



LTEM NO.:U30-04D

(L25.7mm×W7.32mm×H13.85mm / USB-CONNECTORS)



Technical parameter

PROJECT		LEVEL	A[better product]	B[average product]
Electrical Properties	Contact Rating		25mA, 24V DC	
	Initial Contact Resistance		30mΩ max.	50mΩ max.
	Insulation Resistance		100MΩ min.500V DC	Skey/PD: 100MΩ min.300V DC
	Withstand Voltage		500V AC for 1 minute	350 V AC for 1 minut
	There No Load		6,000 Cycles	5,000 Cycles
Durable Performance	Rated Load		5,000 Cycles	4,000 Cycles
	Storage temp.		-25℃~+75℃(Operating Temp:)	

表面插装 DIP


側向導入 LATERAL

精密部品 NICETY

可靠 STABILIZE

適合環保 RoHS

Unit:mm




Operating Force

Inward
Exiting

10. 0N (100grams) ±200gf
10. 0N±300gf



邀您使用(微信)小程序
硕方电子开关&连接器选型手册
手机扫码即可进入...



#1	#2	#3	#4	#5	#6	#7	#8	#9
VBUS	D-	D+	GND	StdA SSRX-	StdA SSRX+	GND DRAIN	StdA SSTX-	StdA SSTX+

Pin Definition



Material declaration

No.	NAME	Type	Description
① A	胶芯	1	LCP 热塑性[蓝色]
② B	接触端子	9	磷铜 C5191 (镀金 1u" /焊区雾锡)
③ C	外壳	1	黄铜 C2680/SPCC[镀镍 50u" min]

UNLESS OTHERWISE SPECIFIED TOLERANCES		
		METRIC
X.	+/-	0.35
.X	+/-	0.25
.XX	+/-	0.25
FRACTIONS	+/-	
ANGLES	+/-	2.00°
DIMENSIONS		
(METRIC)		(MM)

注記 NOTICE

1. 碩方公司擁有最終解釋權; The SOFNG company reserves the right of final interpretation;
2. 文件禁止外洩、轉載; Leaked and reproduced prohibited;
3. 未經授權修改無效。Modify is invalid.

1. 毛刺不可超過 0.02mm;
2. 產品清潔、無雜質、無縮水、無變形及其他
明顯瑕疵;
3. 材質: 塑膠 PC+15%GF, 嵌鋼片 SUS301;
4. 未標注尺寸依照 3D 文档; 未標注公差參考圖
面公差表;
5. 帶▲標注為重點管制尺寸。

本品不屬於危害性廢棄物,須丟棄時可以委託
回收商予以回收再生處理。
Products do not belong to •

運送時本產品不要直接與水、酸鹼性化學物質
接觸,或放置於含有以上氣體環境中,並且需要
注意會有滑落、側翻的危險發生; 運輸過程中
不能有碰撞或者擠壓,須保證溫度與濕度適中
[常溫 25℃,濕度在 50℃以內],不可導致材料變
形或氧化。