







ABIDE BY ROHS

3.8±0.05

ITEM	H	
01	7.3	√
02	7.5	



P. C. B. Layout



Circuit Diagram

Remarks:

1. Rated current、Voltage: DC 12V 50mA
2. Contact resistance: $\leq 100\text{m}\Omega$
3. Insulation resistance: $\geq 100\text{M}\Omega$
4. The intensity of operations: 260±50gf
5. Life requirements: 100000 times
6. Withstand voltage: AC 250V 1 minute
7. All materials comply with RoHS standards

5	Button	PC	1	Black
4	Cover	Q195	1	Cu-Sn Plating
3	Shrapnel	SUS301	1	Ag Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	4	Ag Plating
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE		浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		X≤1	±0.05		
设计 DESIGN		1≤X≤5	±0.10	产品名称 TITLE	轻触开关
审核 CHECKED		5≤X≤10	±0.15		
		X>10	±0.25	产品型号 MODEL	12*12*H方头插脚
校准化 STANDARD		重量 WT.			
批准 APPROVALS		产地 PRODUCTION		产品编码 PART NO	ES1203-10XX-73X-26-A-BF
		视角 PROJ		比例 SCALE	: 页码 SHEET
					1 OF 1