

REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	02/09/2022	PECK


4	DUST COVER	1	THERMOPLASTIC UL94V-0
3	CONTACTS	19	COPPER ALLOY, GOLD PLATED OVER NICKEL ON CONTACT AREA AND 100u" MIN. TIN PLATED OVER NICKEL ON SOLDER TAILS
2	HOUSING	1	THERMOPLASTIC UL94V-0
1	SHELL	1	SPCC,NICKEL PLATED
ITEM	NAME	Q'TY	NOTES









SPECIFICATIONS

- 1.OPERATING CURRENT: 0.5A MAX.
- 2.OPERATION TEMPERATURE: -25~C TO +85~C
- 3.DIELECTRIC WITHSTANDING VOLTAGE:
500Volts AC BETWEEN ADIACENT TERMINAL(UNMATE)
300Volts AC BETWEEN ADIACENT TERMINAL(MATE)
- 4.INSULATION RESISTANCE:
100Mohm MIN.(UNMATED);10Mohm MIN.(MATED)
- 5.HDMI SPECIFICATION COMPLIANCE
- 6.盐雾测试: 国际标准要求, 温度35℃, 浓度5%的盐水, 24H, 用清水洗净后观测, 产品无氧化、无锈蚀
- 7.寿命测试: ≥10000次

DIMENSION CLASSIFICATION ■ : CRITICAL ☒ : MAJOR		台灣碩方精密電子科技有限公司 TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD			
		TITLE	HDMI-019L-L1 立贴式HDMI连接器	開關, 連接器 SOFNG	
TOLERANCE TABLE		PART NO.			SERIES SD106
.X	± 0.40	APPROVED	Peck	DWG NO.	HDMI-019L-L
.XX	± 0.25	CHECKED	Paul	SCALE 1:1	UNIT mm SIZE A4
.XXX	± 0.10	DRAWIN	David	REV	AO SHEET NO. 1/1
ANGLE	± 2°				



WITHOUT COVER



RECOMMENDED PCB LAYOUT(T=1.60mm)
TOP VIEW