



POGO PIN	REAC/ROHS

REV	ECN NO	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2018.06.12












otes:
Characteristics:
A. Material (材料)
1) Housing:High Plastic BLACK (UL94V-0)
2) Plunger:brass c3604
B. Plating (电镀)
1) Plunger:Brass,Plating 3u' Au over Min. 50u' Ni.
C. Electrical (电器性能)
1) Operating voltage: 12V Max.
2) Opetating current: 1A Max.
3) Contact resistance: 30mohm Max.
at working height(Quiescence).
D. Environmental (工作环境)
1) Storage and operating temoperature range:
-40°C~+85°C
2) Humidity range: 10% RH to 90% RH
3) Salt spray: 48H
E. Others (其它)
1) The dimensions marked * are critical,
Should be checked in production
2) RoHS compliant product.





			GENERAL TOLERANCE	
			≥0~2<	±0.15
DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0.25
CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0.15
APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35

FIRST VIEW



SCALE	1:1	UNIT	mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

SAMZO COMPONENTS
Electronic switch and connector manufacturer

TITLE:: 8MM 圆形 PA4.9 H8.0
DWG NO: GA0114-P001
PART NO: GA0114230759
MODEL NO: PG8L-4725-C-F
NAME: POGO PIN