





SECTION A-A



TOLERANCE: ±0.05

- NOTES:
1. MATERIAL:
HOUSING: SEE P/NJUL94V-0;
COVER:H-TEMP PLASTIC;UL94V-0;
CONTACT: COPPER ALLOY;
PEG: COPPER ALLOY;
 2. PLATING:
CONTACT: SN/AU PLATED ON NICKEL OVERALL;
PEG: TIN PLATED ON NICKEL OVERALL.
 3. RATING:
CURRENT RATING: 1.0A AC/DC
VOLTAGE RATING: 125V AC/DC
TEMPERATURE RANGE: -25°C~+85°C;
 4. PART NO.(P/N):

				PIN	A	B	C
PIN	A	B	C	09	10.00	16.00	11.80
02	1.25	7.25	3.05	10	11.25	17.25	13.05
03	2.50	8.50	4.30	11	12.50	18.50	14.30
04	3.75	9.75	5.55	12	13.75	19.75	15.55
05	5.00	11.00	6.80	13	15.00	21.00	16.80
06	6.25	12.25	8.05	14	16.25	22.25	18.05
07	7.50	13.50	9.30	15	17.50	23.50	19.30
		14.75	10.55	16	18.75	24.75	20.55

东莞市高钺达电子科技有限公司

APPROVALS

DR: 刘工

CHKD: 张工

APPD:

DATE

TOLERANCES UNLESS OTHERWISE SPECIFIED

X.±0.30

.X±0.25

.XX±0.20

X.±5°

.X±3°

.XX±1°

NAME(INTENDED USE)

WAF1. 25立贴

PART NO.:

WAFxx-T1T1-2020-A

DRAWING NO.:

SIZE

UNITS

SCALE

SHEET

A4

mm

1:1

1/1