






RoHS



PCB Layout(Pattern side)



Circuit Diagram

FOOT PITCH

CODE	L	L1
C1	6.8	7.5
C2	7.5	8.5

OPERATING FORCE

CODE	VIGOR
B1	120±50gf
B2	180±50gf
B3	250±50gf

SHRAPNEL

CODE	MATERIAL/QTY
D2	SUS/1PCS
D4	SUS/2PCS

TOTAL HEIGHT

CODE	H	ø	CODE	H	ø
A1	3.8	2.15	A6	6.0	2.05
A2	4.3	2.15	A7	6.5	2.05
A3	4.5	2.15	A8	7.0	2.00
A4	5.0	2.10	A9	7.5	1.95
A5	5.5	2.10	A10	8.0	1.95

Ⓕ	Waterproof mat		1	Silica gel	Black
Ⓔ	Terminal		4	Brass(0.3t)	Silvering
Ⓓ	Reed		1	SUS	Silver plating
Ⓒ	Button		1	PPA	Black
Ⓑ	Cover		1	PPA	Black
Ⓐ	Base		1	PPA	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	TACT SWITCHS
Review	date	name	TS-1008S-A□B□-C□D□
Approved	date	name	

Drawing number: A4

modify Review Approved Tolerance not specified Proportion 1:1 unit mm gage number