


客户图

NO.	ECN NO.	DESCRIPTION	DATE
1			



Note:

1: Material(材料):

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

2: Plating(电镀):

Barrel: 2u' Au over 50~100u' Cu over 50~120u' Ni

(针管: 镀金2u', 铜底50~100u', 镍底50~120u'.)

Plunger: 2u' Au over 50~100u' Cu over 50~120u' Ni

(针头: 镀金2u', 铜底50~100u', 镍底50~120u'.)

Spring: No plated (弹簧: 不电镀)

3: Electrical(电气特性):

Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical(机械性能):

Force: 90g±20% at working height. (90g±20% 在工作高度时)。

Durability: 10.000 cycles(min) (寿命: 10,000次)

5: WorkTemperature(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: - 40℃ ~ + 85℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:		DWG. NO.	YZP0865-30076-01
SHEET:	1 of 1	PROJECTION		LENGTH		ANGLE		CHECKED BY:		TITLE:	Pogo pin
DATE:	2024.2.19	VER.	A.0	X.XX ±0.05mm	X.XX ±0.50°	X.X ±0.10mm	X.X ±1.00°	APPROVED BY:			
				X. ±0.20mm	X. ±2.00°						