


NO.	ECN NO.	DESCRIPTION	DATE
1			

客户图



Note:

- Material(材料):
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
- Plating(电镀):
Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'.)
Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)
Ball bear: 2u' Au over 50~80u' Ni(钢珠: 镀金2u', 镍底50~80u'.)
Spring: Gold plated (弹簧: 镀金)
- Electrical(电气特性):
Rated Current & Voltage: DC 12V;5A (额定电压&电流: 直流12V,5A)
Contact Resistance: 100 mohm Max. at working height.
接触电阻: 最大100毫欧 (在工作高度状态下)
- Mechanical(机械性能):
Force: $100g \pm 20\%$ at working height. ($100g \pm 20\%$ 在工作高度)。)
Durability: 10.000 cycles(min) (寿命: 10000次)
- WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: $-20^{\circ}\text{C} \sim +70^{\circ}\text{C}$

深圳市鑫扬泽电子有限公司



HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2024.3.14	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	$\pm 0.05\text{mm}$	X.XX	$\pm 0.50^{\circ}$
X.X	$\pm 0.10\text{mm}$	X.X	$\pm 1.00^{\circ}$
X.	$\pm 0.20\text{mm}$	X.	$\pm 2.00^{\circ}$

DESIGNED BY:		DWG. NO.	YZP0810-20074-02
CHECKED BY:		TITLE:	Pogo pin
APPROVED BY:			