


## 客户图

| NO. | ECN NO. | DESCRIPTION | DATE |
|-----|---------|-------------|------|
| 1   |         |             |      |



Note:

## 1: Material(材料):

Barrel: Brass C3604(针管: 黄铜 C3604)

Plunger: Brass C3604(针头: 黄铜 C3604)

bead: Zirconium oxide (珠子: 氧化锆)

Spring: SUS304 (弹簧: SUS304)

## 2: Plating(电镀):

Barrel: 5u' Au over 50~80u' Ni(针管: 镀金5u', 镍底50~80u'。)

Plunger: 5u' Au over 50~80u' Ni(针头: 镀金5u', 镍底50~80u'。)

Bearing ball: No plated. (氧化锆陶瓷珠: 不电镀)

Spring: Gold flash(弹簧: 镀金)

## 3: Electrical(电气特性):

Rated Current &amp; Voltage: DC 4V;10A (额定电压&amp;电流: 直流4V, 10A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

## 4: Mechanical(机械性能):

Force: 60g ± 20% at working height. (60g ± 20% 在工作高度)。

Durability: 10.000 cycles(min) (寿命: 10000次)

## 5: WorkTemperture(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: - 20℃ ~ + 70℃

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL: 0755-28773277 FAX: 0755-28891353



|        |           |            |     |
|--------|-----------|------------|-----|
| SCALE: | N/A       | UNIT       | mm  |
| SHEET: | 1 of 1    | PROJECTION |     |
| DATE:  | 2024.11.6 | VER.       | A.0 |

THE UNMARKED TOLERANCE ARE AS BELOW:

| LENGTH |         | ANGLE |        |
|--------|---------|-------|--------|
| X.XX   | ±0.05mm | X.XX  | ±0.50° |
| X.X    | ±0.10mm | X.X   | ±1.00° |
| X.     | ±0.20mm | X.    | ±2.00° |

|              |  |          |                  |
|--------------|--|----------|------------------|
| DESIGNED BY: |  | DWG. NO. | YZP0894-25093-01 |
| CHECKED BY:  |  | TITLE:   | Pogo pin         |
| APPROVED BY: |  |          |                  |