




- 1: Material(材料) :
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
- 2: Plating(电镀) :
Barrel: 3u' Au over 50~100u' Ni (针管: 镀金3u', 镍底50~100u'.)
Plunger: 3u' Au over 50~100u' Ni (针头: 镀金3u', 镍底50~100u'.)
Spring: Not plated. (不电镀)
- 3: Electrical(电气特性) :
Rated Current & Voltage: DC 12V;2A (额定电压&电流: 直流12V, 2A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
- 4: Mechanical(机械性能) :
Force: 50g±20% at working height. (50g±20% 在工作高度)。
Durability: 10.000 cycles(min) (寿命: 10000次)
- 5: WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: - 20℃~ + 70℃

深圳市鑫扬泽电子有限公司



TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2022.1.4	VER.	

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZF0058-21075-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			