

Note:

- 1: Material(材料):
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
Bear ball: Sus304 (钢珠: Sus304)
- 2: Plating(电镀):
Barrel: 1u' Au over 50~80'u Ni (针管: 镀金1u', 镍底50~80u')
Plunger: 1u' Au over 50~80'u Ni (针头: 镀金1u', 镍底50~80u')
Spring: Gold flash (弹簧: 镀金)
Bear ball: 2u' Au (钢珠: 镀金2u')
- 3: Electrical(电气特性):
Rated Current & Voltage: DC 12V;6A (额定电压&电流: 直流12V, 6A)
Contact Resistance: 100 mohm Max. at working height.
接触电阻: 最大100毫欧 (在工作高度状态下)
- 4: Mechanical(机械性能):
Force: 130g $\pm$ 20% at working height. (130g $\pm$ 20% 在工作高度)。
Durability: 10.000 cycles(min) (寿命: 10000次)
- 5: WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: -20℃~ +70℃