


NO.	ECN NO.	DESCRIPTION	DATE
-----	---------	-------------	------



Note:

1: Material(材料) :

Barrel: lead-free brass C6801 (针管: 无铅铜 C6801)

Plunger: lead-free brass C6801 (针头: 无铅铜 C6801)

Spring: SUS304 (弹簧: SUS304)

2: Plating(电镀) :

Barrel: 5u' Au over 200u' Cu over 200u' Ni

(针管: 镀金5u', 铜底200u', 镍底200u'.)

Plunger: 5u' Au over 200u' Cu over 200u' Ni

(针头: 镀金5u', 铜底200u', 镍底200u'.)

Spring: No plated (弹簧: 不电镀)

3: Electrical(电气特性) :

Rated Current & Voltage: DC 12V/1A (额定电压&电流: 直流12V,1A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical(机械性能) :

Force: 120g±20% at working height. (120g±20% 在工作高度)。

Durability: 10.000 cycles(min) (寿命: 10000次)

5: WorkTemperature(工作环境):

Withstanding Higt Temperature: 280t

Operational Temperature: -40t~ +85t

深圳市鑫扬泽电子有限公司									
TEL: 0755-28732277 FAX: 0755-28891353									
HTTP://WWW.XYZO6OPIN.COM									
									
SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :					
SHEET:	1 of 1	PROJECTION		LENGTH		ANGLE			
DATE:	2023.12.27	VER.	D.0	X.XX X.X X.X	±0.05mm ±0.10mm ±0.20mm	X.XX X.X X.	±0.50° ±1.00° ±2.00°	CHECKED BY:	DWG. NO.
				APPROVED BY:				TITLE:	YZP0788-20067-04
								Pogo pin	



深圳市鑫扬泽电子有限公司
HTTP://WWW.XYZFOGOPIN.COM
TEL:0755-28773277 FAX:0755-28891353