


客户图



- Note:
- Material(材料) :
 Barrel: Brass C3604 (针管: 黄铜 C3604)
 Plunger: Brass C3604 (针头: 黄铜 C3604)
 Spring: SUS304 (弹簧: SUS304)
 Ball bear :SUS304 (钢珠: SUS304)
 - Plating(电镀) :
 Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'。)
 Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'。)
 Ball bear: 2u' Au over 50~80u' Ni(钢珠: 镀金2u', 镍底50~80u'。)
 Spring: Gold flash (弹簧: 镀金)
 - Electrical(电气特性) :
 Rated Current & Voltage: DC 12V;5A (额定电压&电流: 直流12V, 5A)
 Contact Resistance: 50 mohm Max. at working height.
 接触电阻: 最大50毫欧 (在工作高度状态下)
 - Mechanical(机械性能) :
 Force: 120g±20% at working height. (120g±20%在工作高度)。
 Durability: 10.000 cycles(min) (寿命: 10000次)
 - WorkTemperature(工作环境):
 Withstanding Higt Temperature: 280℃
 Operational Temperature: - 20℃~ + 70℃

深圳市鑫扬泽电子有限公司



TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2022.12.26	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZP0741-25095-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			