


客户图

NO.	ECN NO.	DESCRIPTION	DATE



Note:

1: Material(材料):

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

2: Plating(电镀):

Barrel: 5u' Au over 200u' Cu over 200u' Ni (针管: 镀金5u', 铜底200u', 镍底200u'.)

Plunger: 5u' Au over 200u' Cu over 200u' Ni (针头: 镀金5u', 铜底200u', 镍底200u'.)

Spring: NO plated (弹簧: 不电镀)

3: Electrical(电气特性):

Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V, 1A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical(机械性能):

Force: 100g $\pm$ 20% at working height. (100g $\pm$ 20%在工作高度时)。

Durability: 10.000 cycles(min) (寿命: 10,000次)

5: WorkTemperature(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: -20℃~ +70℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277

FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2023.12.6	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW:

LENGTH	ANGLE
X.XX ± 0.05 mm	X.XX $\pm 0.50^\circ$
X.X ± 0.10 mm	X.X $\pm 1.00^\circ$
X. ± 0.20 mm	X. $\pm 2.00^\circ$

DESIGNED BY:		DWG. NO.	YZP0831-32066-02
CHECKED BY:		TITLE:	Pogo pin
APPROVED BY:			