


NO.	ECN NO.	DESCRIPTION	DATE
1			

客户图



Note:

1: Material(材料) :

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

2: Plating(电镀) :

Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'。)

Plunger: 5u' Platinum over 3'u Au over 70~120'u Ni (针头: 镀铂

5u', 金底3u', 镍底70~120u'。)

Spring: Gold flash (弹簧: 镀金)

3: Electrical(电气特性) :

Rated Current & Voltage: DC 12V;2A (额定电压&电流: 直流12V,2A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical(机械性能) :

Force: 60g±20% at working height. 60g±20% 在工作高度)。

Durability: 10.000 cycles(min) (寿命: 10000次)

5: WorkTemperature(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: -20℃~ +70℃



深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZFOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:	DWG. NO.	YZP0722-20108-04
SHEET:	1 of 1	PROJECTION		LENGTH		ANGLE		CHECKED BY:	TITLE:	
DATE:	2023.4.12	VER.	A.0	X.XX X.X	±0.05mm ±0.10mm ±0.20mm	X.XX X.X	±0.50° ±1.00° ±2.00°	APPROVED BY:	Pogo pin	