


NO.	ECN NO.	DESCRIPTION	DATE
1			

客户图



Note:

- 1: Material(材料):
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
ball bearing: SUS 304 (钢珠: 不锈钢 304)
Spring: SUS304 (弹簧: SUS304)
- 2: Plating(电镀):
Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'。)
Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'。)
ball bearing: 2u' Au over 50~80u' Ni (钢珠: 镀金2u', 镍底50~80u'。)
Spring: Gold flash (弹簧: 镀金)
- 3: Electrical(电气特性):
Rated Current & Voltage: DC 12V;5A (额定电压&电流: 直流12V, 5A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
- 4: Mechanical(机械性能):
Force: 120g±20% at working height. (120g±20% 在工作高度)。
Durability: 10.000 cycles(min) (寿命: 10000次)
- 5: WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: - 20℃~ + 70℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:		DWG. NO.	YZP0870-32082-01
SHEET:	1 of 1	PROJECTION						LENGTH		ANGLE	
DATE:	2024.3.25	VER.	D.0	X.XX X.X X.	±0.05mm ±0.10mm ±0.20mm	X.XX X.X X.	±0.50° ±1.00° ±2.00°	APPROVED BY:			