





NO.	ECN NO.	DESCRIPTION	DATE



RECOMMENDED PCB LAYOUT

Note:

1: Material (材料):

Housing: PA46+30%GF (胶芯: PA46)

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧 SUS304)

2: Plating (电镀):

Barrel: 3u' Au over 50~80u' Ni

(针管: 镀金3u', 镍底50~80u'.)

Plunger: 3u' Au over 50~80u' Ni

(针头: 镀金3u', 镍底50~80u'.)

Spring: No plated (弹簧: 不电镀)

3: Electrical (电气特性):

Rated Current & Voltage: DC 12V;1A

(额定电压&电流: 直流12V,1A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

Insulation Resistance: 1,000MΩ minimum.

(绝缘电阻: 1,000MΩ以上)

Dielectric Withstand Voltage: 500VAC/minute.

(抗电压: 500VAC/minute)

4: Mechanical (机械性能):

Force: 30g±20% at working height.

(30g±20% 在工作高度)。

Durability: 10,000 cycles (min) (寿命: 10000次)

5: Work Temperature (工作环境):

Withstanding Hight Temperature: 280℃

Operational Temperature: -20℃~ +70℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2023.2.4	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH	ANGLE
X.XX ±0.05mm	X.XX ±0.50°
X.X ±0.10mm	X.X ±1.00°
X. ±0.20mm	X. ±2.00°

DESIGNED BY:		DWG. NO.	YZP0684-17047-08020-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			