


NO.	ECN NO.	DESCRIPTION	DATE
1			

客户图



Note:

- Material(材料):
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
bead: Zirconium oxide (珠子: 氧化锆)
Spring: SUS304 (弹簧: SUS304)
- Plating(电镀):
Barrel: 5u' Au over 50~80u' Ni (针管: 镀金5u', 镍底50~80u'.)
Plunger: 5u' Au over 50~80u' Ni (针头: 镀金5u', 镍底50~80u'.)
Bearing ball: No plated. (氧化锆陶瓷珠: 不电镀)
Spring: Gold flash (弹簧: 镀金)
- Electrical(电气特性):
Rated Current & Voltage: DC 24V;3A (额定电压&电流: 直流24V, 3A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
- Mechanical(机械性能):
Force: 150g±20% at working height. (150g±20% 在工作高度).
Durability: 10.000 cycles(min) (寿命: 10000次)
- WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: - 20℃~ + 70℃

深圳市鑫扬泽电子有限公司



HTTP://WWW.XYZPOGOPIN.COM

TEL: 0755-28773277 FAX: 0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2023.4.6	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZP0773-20093-01
CHECKED BY:		TITLE:	Pogo pin连接器
APPROVED BY:			