




客户图

NO.	ECN NO.	DESCRIPTION	DATE
1			



RECOMMENDED PCB LAYOUT

Note:

- Material (材料):
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
- Plating (电镀):
Barrel: 5u' Au over 200' Cu over 200u' Ni (针管: 镀金5u', 铜底200u', 镍底200u'.)
Plunger: 5u' Au over 200u' Cu over 200u' Ni (针头: 镀金5u', 铜底200u', 镍底200u'.)
Spring: Gold plated (弹簧: 镀金)
- Electrical (电气特性):
Rated Current & Voltage: DC 5V; 1.5A (额定电压&电流: 直流5V, 1.5A)
Contact Resistance: 50 mohm Max. at working height. 接触电阻: 最大50毫欧 (在工作高度状态下)
- Mechanical (机械性能):
Force: 100g±20% at working height. (100g±20%在工作高度时).
Durability: 10,000 cycles(min) (寿命: 10,000次)
- Work Temperature (工作环境):
Withstanding Hight Temperature: 280°C
Operational Temperature: -20°C ~ +70°C

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL: 0755-28773277 FAX: 0755-28891353



SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:		DWG. NO.	YZP0868-22068-02
SHEET:	1 of 1	PROJECTION		LENGTH		ANGLE		CHECKED BY:		TITLE:	Pogo Pin
DATE:	2024.3.1	VER.	A.0	X.XX	±0.05mm	X.XX	±0.50°	APPROVED BY:			
				X.X	±0.10mm	X.X	±1.00°				
				X.	±0.20mm	X.	±2.00°				