





SPECIFICATIONS

- 1、Current Rating: 5A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material:Wafer PBT/PA66,UL94V-0 Black  
PIN Brass Tin-plated


| PIN     | 尺寸 (mm) |       |
|---------|---------|-------|
|         | A       | B     |
| -2*01AW | ---     | 6.10  |
| -2*02AW | 3.00    | 9.10  |
| -2*03AW | 6.00    | 12.10 |
| -2*04AW | 9.00    | 15.10 |
| -2*05AW | 12.00   | 18.10 |
| -2*06AW | 15.00   | 21.10 |
| -2*07AW | 18.00   | 24.10 |
| -2*08AW | 21.00   | 27.10 |
| -2*09AW | 24.00   | 30.10 |
| -2*10AW | 27.00   | 33.10 |
| -2*11AW | 30.00   | 36.10 |
| -2*12AW | 33.00   | 39.10 |

|      |    |      |       |             |    |     |     |              |              |                        |
|------|----|------|-------|-------------|----|-----|-----|--------------|--------------|------------------------|
| 更改记录 | 标记 | 变更内容 | 签名/日期 | 未注公差        | 单位 | mm  | 标准化 | 签名/日期        | 品名           | 557 ( 3.0 ) 双排弯针-2*NAW |
|      |    |      |       | X.X ±0.30   | 版本 | A   | 编制  | 周少华 21.09.25 | 图号           | ZJLQ-2xNAW43045        |
|      |    |      |       | X.XX ±0.20  | 比例 | 1:1 | 审核  | 赵先礼 21.09.25 | 浙江领强电子科技有限公司 |                        |
|      |    |      |       | X.XXX ±0.10 | 投影 |     | 批准  | 田泽民 21.09.25 |              |                        |
|      |    |      |       | Angle ±3.0° | 页次 | 1/1 |     |              |              |                        |


双排弯针P位结构示意图




2x1AW




2x6AW




2x7AW




2x10AW




2x2AW




2x5AW




2x8AW




2x11AW




2x3AW



2x4AW



2x9AW



2x12AW

|      |    |      |       |                |    |                                                                                       |     |                   |    |                        |
|------|----|------|-------|----------------|----|---------------------------------------------------------------------------------------|-----|-------------------|----|------------------------|
| 更改记录 | 标记 | 变更内容 | 签名/日期 | 未注公差           | 单位 | mm                                                                                    | 标准化 | 签名/日期             | 品名 | 557 ( 3.0 ) 双排弯针-2*NAW |
|      |    |      |       | X. X    ±0. 30 | 版本 | A                                                                                     | 编制  | 周少华    21. 09. 25 | 图号 | ZJLQ-2xNAW43045        |
|      |    |      |       | X. XX   ±0. 20 | 比例 | 1: 1                                                                                  | 审核  | 赵先礼    21. 09. 25 |    |                        |
|      |    |      |       | X. XXX ±0. 10  | 投影 |  | 批准  | 田泽民    21. 09. 25 |    |                        |
|      |    |      |       | Angle ±3. 0°   | 页次 | 1/1                                                                                   |     |                   |    |                        |

浙江领强电子科技有限公司