






客户图



RECOMMENDED PCB LAYOUT

NO.	ECN NO.	DESCRIPTION	DATE

Note:

- 1: Material(材料):
Housing: PA9T(胶芯:PA9T)
Pin: Brass C3604 (针: 黄铜 C3604)
Magnet: NdFeB (磁铁: 钕铁硼)
- 2: Plating(电镀):
Pin: 3u' Au over 50u'~80u' Ni(针: 镀金3u', 镍底50u'~80u'.)
Magnet: Nickel plating(镀镍)
- 3: Electrical(电气特性):
Rated Current & Voltage: DC 12V;3A (额定电压&电流: 直流12V,3A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
Insulation Resistance: 1,000MΩ minimum. (绝缘电阻: 1,000MΩ以上)
Dielectric Withstand Voltage: 500VAC/minute. (抗击电压: 500VAC/minute)
- 4: WorkTemperature(工作环境):
Withstanding Hight Temperature: 280℃
Operational Temperature: -20℃~ +70℃

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2025.1.13	VER.	A.1

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZT0755-20028-02025-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			