




NOTES

1.MATERIAL

- 1.1 HOUSING: THERMOPLASTIC. UL94V-0. COLOR: BLACK
- 1.2 CONTACT: HIGH-PERFORMANCE COPPER ALLOY.
- 1.3 LATCH: STAINLESS STEEL.
- 1.4 PEG: STAINLESS STEEL.

2.FINISH

- 2.1 CONTACT: GOLD PLATING (SEE P/N) ON CONTACT AREA AND 1~3u" GOLD PLATING ON SOLDER AREA NICKEL 50~150u" UNDER-PLATING ALL OVER
- 2.2 PEG: 50~150u" TIN PLATING OVER 50~150u" NICKEL UNDER-PLATING ALL OVER

3.MSL LEVEL: MSL (MOISTURE SENSITIVITY LEVEL)=1.

4.PRODUCT NUMBER NOTE:

D5262-52 XX R R


52: 5.2mm HEIGHT

CONTACT AREA PLATING

01: G/F
10: 10u" Au
15: 15u" Au

PACKING OPTIONS
R: TAPE & REEL

ORIENTATION
S: STANDARD
R: REVERSE



MATING: ① INSERTING → ② ROTATING → ③ FIXED



UNMATING: ④ UNFIXED → ⑤ ROTATING → ⑥ WITHDRAWING

MATING/UNMATING VIEW
SCALE 2:1







TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED		APPD: Jason MAT'L: CHKD: Schumi FINISH: DRWN: Lei Songping Q'TY:	
LINEAR	ANGLES				
X±0.40	X°±				
.X±0.30	.X°±				
.XX±0.20	.XX°±				
.XXX±0.10	.XXX°±				

TITLE: DDR5 SODIMM 5.2H 262PIN REVERSE TYPE.					
PART NO. D5262-52XXRR					
DWG NO. C-D5262-52R					
UNITS	SCALE	SHEET	REV		
MM	1 : 1	1 OF 2	A		

REV	ECN NO.	NAME	DATE	.XXX±0.10	.XXX°±
A	-----	FENG.PF	Nov.09.2023	.XX±0.20	.XX°±



RECOMMEND MODULE CONFIGURATION



TOLERANCE		UMax 东莞市友贸实业有限公司 conn DONGGUAN UMAX ENTERPRISE LIMITED	
LINEAR	ANGLES		
X.±0.40	X°±	APPD: Jason	MAT'L:
.X±0.30	.X°±	CHKD: Schumi	FINISH:
.XX±0.20	.XX°±	DRWN: Lei Songping	Q'TY:
.XXX±0.10	.XXX°±		

TITLE: DDR5 SODIMM
 5.2H 262PIN REVERSE TYPE.

PART NO. D5262-52XXRR

DWG NO. C-D5262-52R

UNITS	SCALE	SHEET	REV
MM	1 : 1	2 OF 2	A

REV	ECN NO.	NAME	DATE
	SEE SHEET 1		