




技术参数 SPECIFICATIONS

间距 (Pitch): 1.25mm

极数 (Poles): 4~40

额定电压 (Voltage rating): 50V DC/AC

额定电流 (Current rating): 0.5A DC/AC

耐压值 (Withstand Voltage): 500VAC/m

工作温度 (Working Temperature): -25℃~+85℃

绝缘电阻 (Insulation Resistance): ≥500MΩ

接触电阻 (Contact resistance): ≤30mΩ


材料 Material

接触件 (Contact): 磷青铜 镀亮锡(镍Ni30~80u",锡Sn80~200u")
t=0.25mm Phosphor Bronze Tin-plated

塑胶主体 (Housing): PA66 (UL94V-0)

Heat resistance plastic: PA66 (UL94V-0)

Poles.	PART. NO.	A	B	C
4P	F-FPC2R04P-E320	8.55	6.35	3.75
5P	F-FPC2R05P-E320	9.80	7.60	5.00
6P	F-FPC2R06P-E320	11.05	8.85	6.25
7P	F-FPC2R07P-E320	12.30	10.10	7.50
...		...	...	...
39P	F-FPC2R39P-E320	52.30	50.10	47.50
40P	F-FPC2R40P-E320	53.55	51.35	48.75



PCB LAYOUT

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO., LTD					
CHECKED:	DATE:	TITLE: FPC1.25-XP 弯插 单触 正脚位 米白色					
DRAWN: YKX	DATE: 2024-07-15	PART. NO.		F-FPC2RXXP-E320			
		UNIT	mm	SCALE	free		
		FILE NO.		Ckmtw-FPC-D002		REV.	A
						LX00	