








NOTES

1.MATERIAL

1.1 HOUSING: THERMOPLASTIC. UL94V-0. COLOR: BLACK

1.2 CONTACT: HIGH-PERFORMANCE COPPER ALLOY.

1.3 LATCH: STAINLESS STEEL.

1.4PEG: STAINLESS STEEL.

2.FINISH

2.1CONTACT: GOLD PLATING(SEE P/N) ON CONTACT AREA AND
1~3u" GOLD PLATING ON SOLDER AREA NICKEL
50~150u" UNDER-PLATING ALL OVER

2.2 PEG: 50~150u" TIN PLATING OVER

50~150u" NICKEL UNDER-PLATING ALL OVER

3.MSL LEVEL:MSL(MOISTURE SENSITIVITY LEVEL)=1.

4.PRODUCT NUMBER NOTE:

D5262-92 XX S R

52: 5.2mm HEIGHT _____

CONTACT AREA PLATING

01: G/F

10:10u" Au

15:15u" Au

PACKING OPTIONS
R: TAPE&REEL

ORIENTATION

— ORIENTATION
S: STANDARD


R: REVERSE

TOLERANCE		 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED	
LINEAR	ANGLES		
X,±0.40	X°,±		
.X±0.30	.X°±		
.XX±0.20	.XX°±	APPD: Jason	MAT'L:
.XXX±0.10	.XXX°±	CHKD: Schumi	FINISH:
		DRWN: Lei Songping	Q'TY:

TITLE:	DDR5 SODIMM 9.2H 262PIN STANDARD TYPE.
--------	---

PART NO.	D5262-92XXSR
----------	--------------

DWG NO.	C-D5262-92S
---------	-------------



UNITS	SCALE	SHEET	REV
MM	1 : 1	1 OF 2	A

CUSTOMER

