












RECOMMENDED P.C. BOARD PATTERN LAYOUT
RECOMMENDED METAL MASK THICKNESS: T=0.15
ALL TOLERANCES ARE ±0.05

NOTE :
1. TERMINAL : COPPER ALLOY.
2. HOUSING : LCP UL 94V-0 , COLOR : BLACK
PLATING :
1. 1.27μm MIN . NI UNDERPLATING.
2. 0.76μm GOLD PLATING ON CONTACT AREA.
3. 2.54μm MIN . LATCH NI UNDERPLATING.
4. TO PREVENT THE POLLUTION OF THE ENVIRONMENT PRODUCT INFO
ROHS AGREEMENT:IN LINE WITH THE EUROPEAN UNION ROHS.



TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAXCONN ENTERPRISE LIMITED		APPD: Jason MAT'L: CHKD: Schumi FINISH: DRWN: Lucy Q'TY:	
LINEAR	ANGLES				
X±0.30	X'±				
.X±0.25	.X'±				
.XX±0.15	.XX'±				
.XXX±0.08	.XXX'±				

TITLE: MINI SAS HD INTEGRATED CONNECTOR, 0.75 PITCH, V/T, SMT TYPE					
PART NO.		91911-111301P			
DWG NO.		c-91911			
	UNITS	SCALE	SHEET	REV	
	MM	1 : 1	1 OF 1	A1	

REV	ECN NO.	NAME	DATE
		Lei Songping	May,22.2016