



标“*”为重点检验尺寸

所用物料均符合ROHS标准




MATERIALS AND FINISH

SHELL : STEEL MATERIAL, FRONT NICKEL FINISHED
BACK SHELL TIN FINISHED
INSULATOR : PBT THERMOPLASTIC, 30% GLASS
FILLED, UL 94V-0 RATED, BLACK COLOR
CONTACT MATERIAL : PHOSCU
CONTACT FINISH : FULL GOLD 1u" FINISHED
#4-40 THREADED RIVETS

ELECTRICAL CHARACTERISTICS

CONTACT CURRENT RATING : 5.0 AMPS
CONTACT RESISTANCE : 30 MILLIOHMS MAX.
DIELECTRIC WITHSTANDING VOLTAGE : 1000 V AC MIN.
INSULATION RESISTANCE : 5000 MEGAOHMS MIN.
TEMPERATURE RATING : -55°C ~ +105°C



未注公差				GDM78M-180-4		比例	1:1
X.	±0.35					幅面	A4
X.X	±0.25						
X.XX	±0.1						
X.XXX	±0.05						
X° ±2°	X.X° ±1°						
A/0 版				料号		设计	Roy
				型号		审核	
				图号		核准	Andy
						日期	2011.8.09
						日期	2011.8.09