






SECTION A-A

技术指标(Technical Index):


- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):100V,AC.
- 3.额定电流(Rated current):1.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
- 6.耐压值(Withstanding voltage):500V AC/minute.




DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*± 5°	APR. Alex	TITLE: ZH1.5##WTB		
.XX±0.2	.X.*± 3°	CHK. Jack	DWG NO. XY-ZH1.5-NA21-BL		
.XXX±0.1	.XX.*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1

序号	品名	材质
①	ZH1.5弯针WTB胶芯	LCP UL94V-0 本色
②	ZH1.5弯针WTB端子	铜合金/表面镀锡

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd



9. 纸箱大小、中、标准型3种规格型号:装箱为整箱(左下包装量)采用标准型纸箱包装,未达到整箱数量以产品适当采用小型或中型纸箱包装。



紙箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Hight (CM)	7.5	15	32

CKT	B0	W	F	S
(1.5mm pitch)				
2	4.80	16	7.50	
3	6.30			
4	7.80			
5	9.30	24	11.50	
6	10.80			
7	12.30			
8	13.80			
9	15.30			
10	16.80	32	14.20±0.10	28.4
11	18.30			
12	19.80			
13	21.30			
14	22.80	44	20.20±0.10	40.4
15	24.30			
16	25.80			
17	27.30			
18	28.80			
19	30.30			
20	31.80			

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.5	X.*± 5°	APR. Alex	TITLE: ZH1.5**WTB				
.XX±0.2	.X*± 3°	CHK. Jack	DWG NO. XY-ZH1.5-NA21-BL				
.XXX±0.1	.XX*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING		
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A	