



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100M\Omega$ 。



序号	品名	材质	合高(H)	公座单高	母座单高
①	0.5 Pitch C型单排立式BTB母座底座	LCP UL94 V-0 颜色:米黄色	1.5	1.3	1.4
②	0.5 Pitch C型单排立式BTB母座端子	铜合金/表面镀金	2.0	1.3	1.9
			2.5	1.3	2.4

Part No	CKT	A	B	C
XY-DF519C-10LBMBW	2X5	2.00	3.40	5.50
XY-DF519C-12LBMBW	2X6	2.50	3.90	6.00
XY-DF519C-14LBMBW	2X7	3.00	4.40	6.50
XY-DF519C-16LBMBW	2X8	3.50	4.90	7.00
XY-DF519C-18LBMBW	2X9	4.00	5.40	7.50
XY-DF519C-20LBMBW	2X10	4.50	5.90	8.00
XY-DF519C-22LBMBW	2X11	5.00	6.40	8.50
XY-DF519C-24LBMBW	2X12	5.50	6.90	9.00
XY-DF519C-26LBMBW	2X13	6.00	7.40	9.50
XY-DF519C-28LBMBW	2X14	6.50	7.90	10.00
XY-DF519C-30LBMBW	2X15	7.00	8.40	10.50
XY-DF519C-32LBMBW	2X16	7.50	8.90	11.00
XY-DF519C-34LBMBW	2X17	8.00	9.40	11.50
XY-DF519C-36LBMBW	2X18	8.50	9.90	12.00
XY-DF519C-38LBMBW	2X19	9.00	10.40	12.50
XY-DF519C-40LBMBW	2X20	9.50	10.90	13.00
.....	...	...	...	...
XY-DF519C-100LBMBW	2X50	24.50	25.90	28.00

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*±1°	APR.	Alex	TITLE: 0.5 Pitch C型单排立式BTB母座底座(料号1.4)	
.XX±0.2	.X°±	CHK.	Jack	DWG NO. XY-DF519C-10LBMBW	
.XXX±0.1	.XX°±	DRA.	Can	PROJ. CUSTOMER DRAWING	
		SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A