








常规2 Pin样式



SECTION A-A







技术指标(Technical Index):

1. 温度范围(Temperature range): -25°C~+85°C.
2. 额定电压(Rated voltage): 250V, AC.
3. 额定电流(Rated current): 3.0A AC, DC.
4. 接触电阻(Contact resistance): $\leq 20m\Omega$.
5. 耐压值(Withstanding voltage): 1000V AC/minute.
6. 绝缘电阻(Insulation resistance): $\geq 1000M\Omega$.

Part No	CKT	A	B
XY-XH2.54-2A11-BL	2	2.5	7.5
XY-XH2.54-3A11-BL	3	5.0	10.0
XY-XH2.54-4A11-BL	4	7.5	12.5
XY-XH2.54-5A11-BL	5	10.0	15.0
XY-XH2.54-6A11-BL	6	12.5	17.5
XY-XH2.54-7A11-BL	7	15.0	20.0
XY-XH2.54-8A11-BL	8	17.5	22.5
XY-XH2.54-9A11-BL	9	20.0	25.0
XY-XH2.54-10A11-BL	10	22.5	27.5
XY-XH2.54-11A11-BL	11	25.0	30.0
XY-XH2.54-12A11-BL	12	27.5	32.5
XY-XH2.54-13A11-BL	13	30.0	35.0
XY-XH2.54-14A11-BL	14	32.5	37.5
XY-XH2.54-15A11-BL	15	35.0	40.0
XY-XH2.54-16A11-BL	16	37.5	42.5

序号	品名	材质
①	XH2.5直针WTB胶芯	LCP UL94V-0 米色 白色
②	XH2.5直针WTB端子	铜合金/表面镀锡
③	XH2.5立式吸盖	LCP UL94V-0 米色




DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.5	X.*± 5°	APR. Alex	TITLE: XH2.5针WTB			
.XX±0.25	.X.*± 3°	CHK. Jack	DWG NO. XY-XH2.54-NA11-BL			
.XXX±0.15	.XX.*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A



CKT (2.5mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	24	500	10	5000
3				
4				
5				
6	32	500	8	4000
7				
8				
9				
10	44	500	6	3000
11				
12				
13				
14	56	500	5	2500
15				
16				

NOTE(注):

- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
(10片孔距累积公差 $\pm 0.2\text{mm}$.)
- 2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
(载带拱/弯曲MAX:1/100mm.)
- 3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
(所有尺寸要满足EIA-481要求.)
- 4.MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING.
(载带材料: 透明防静电 PS, 冷封.)
- 5.THICKNESS: $0.50 \pm 0.05\text{mm}$. (载带厚度: $0.50 \pm 0.05\text{mm}$.)
- 6.PACKING LENGTH PER REEL: 6.43 METERS. (每卷包装长度: 6.43米.)
- 7.COMPONENT LOAD PER REEL: 500 PCS. (每卷包装数量: 500片.)
8. 纸盒装箱以不超过装箱线为准, 空余位置用塑料泡沫及保尼龙填充.
9. 纸盒分小、中、标准型3种规格型号: 装箱为整箱(左下包装)采用标准型纸盒包装, 未达到整箱数量以产品适当采用小型或中型纸盒包装.



纸盒型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Height (CM)	7.5	15	32

CKT (2.5mm pitch)	B0	W	F	S
2	7.80	24	11.50±0.10	
3	10.30			
4	12.80			
5	15.30			
6	17.80	32	14.20±0.10	28.40
7	20.30			
8	22.80			
9	25.30			
10	27.80	44	20.20±0.10	40.40
11	30.30			
12	32.80			
13	35.30			
14	37.80	56	26.2±0.10	52.40
15	40.30			
16	42.80			

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	.X*±5°	APR.	Alex	TITLE: XH2.5#WTB	
.XX±0.25	.X*±3°	CHK.	Jack	DWG NO. XY-XH2.5-NA11-BL	
.XXX±0.15	.XX*±1°	DRA.	Can	PROJ.  CUSTOMER DRAWING	
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		