







技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 50V. AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100M\Omega$.



High photosynthesis 高(H)	The female seat height (H1)	The male seat height 公座单高(H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

序号	品名	材质
①	0.5 Pitch双排立式BTB母座胶壳	PA10T UL94 V-0 颜色:黑色
②	0.5 Pitch双排立式BTB母座端子	铜合金/表面点镀金
③	0.5 Pitch双排立式BTB母座盖	LCP UL94 V-0颜色:黑色

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: 0.5 Pitch双排立式BTB母座(精3.0)			
.X±0.5	X.*±1°	APR.	Alex	DWG NO. XY-DF530A-NLBMBW	
.XX±0.2	.X*±	CHK.	Jack	CUSTOMER DRAWING	
.XXX±0.1	.XX*±	DRA.	Can	PROJ.	SIZE A4
		SCALE 1:1		SHEET 1/1	REV. A

PIN NO	PIN	DIM A	DIM B	DIM C	DIM E
XY-DF530A-8LMBW	8	1.50	2.55	4.70	4.00
XY-DF530A-10LMBW	10	2.00	3.05	5.20	
XY-DF530A-12LMBW	12	2.50	3.55	5.70	
XY-DF530A-14LMBW	14	3.00	4.05	6.20	
XY-DF530A-16LMBW	16	3.50	4.55	6.70	
XY-DF530A-18LMBW	18	4.00	5.05	7.20	
XY-DF530A-20LMBW	20	4.50	5.55	7.70	
XY-DF530A-22LMBW	22	5.00	6.05	8.20	
XY-DF530A-24LMBW	24	5.50	6.55	8.70	
XY-DF530A-26LMBW	26	6.00	7.05	9.20	
XY-DF530A-28LMBW	28	6.50	7.55	9.70	8.00
XY-DF530A-30LMBW	30	7.00	8.05	10.20	
XY-DF530A-32LMBW	32	7.50	8.55	10.70	
XY-DF530A-34LMBW	34	8.00	9.05	11.20	
XY-DF530A-36LMBW	36	8.50	9.55	11.70	
XY-DF530A-38LMBW	38	9.00	10.05	12.20	
XY-DF530A-40LMBW	40	9.50	10.55	12.70	
XY-DF530A-44LMBW	44	10.50	11.55	13.70	
XY-DF530A-50LMBW	50	12.00	13.05	15.20	
XY-DF530A-60LMBW	60	14.50	15.55	17.70	
XY-DF530A-70LMBW	70	17.00	18.05	20.20	
XY-DF530A-80LMBW	80	19.50	20.55	22.70	
XY-DF530A-100LMBW	100	24.50	25.55	27.70	

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.* ± 1°	APR. Alex	TITLE: 雄 0.5 Pitch 雌 BTB (雄3.0)		
.XX±0.2	.X.* ±	CHK. Jack	DWG NO. XY-DF530A-NLMBW		
.XXX±0.1	.XX.* ±	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1