





技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC.
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



序号	品名	材质
①	0.5 Pitch B型单槽立式BTB公座嵌芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型单槽立式BTB公座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
XY-DF526B-8LBGDW	2X4	1.50	2.60	4.10	3.60
XY-DF526B-10LBGDW	2X5	2.00	3.10	4.60	4.10
XY-DF526B-12LBGDW	2X6	2.50	3.60	5.10	4.60
XY-DF526B-14LBGDW	2X7	3.00	4.10	5.60	5.10
XY-DF526B-16LBGDW	2X8	3.50	4.60	6.10	5.60
XY-DF526B-18LBGDW	2X9	4.00	5.10	6.60	6.10
XY-DF526B-20LBGDW	2X10	4.50	5.60	7.10	6.60
XY-DF526B-22LBGDW	2X11	5.00	6.10	7.60	7.10
XY-DF526B-24LBGDW	2X12	5.50	6.60	8.10	7.60
XY-DF526B-26LBGDW	2X13	6.00	7.10	8.60	8.10
XY-DF526B-28LBGDW	2X14	6.50	7.60	9.10	8.60
XY-DF526B-30LBGDW	2X15	7.00	8.10	9.60	9.10
XY-DF526B-32LBGDW	2X16	7.50	8.60	10.10	9.60
XY-DF526B-34LBGDW	2X17	8.00	9.10	10.60	10.10
XY-DF526B-36LBGDW	2X18	8.50	9.60	11.10	10.60
XY-DF526B-38LBGDW	2X19	9.00	10.10	11.60	11.10
XY-DF526B-40LBGDW	2X20	9.50	10.60	12.10	11.60
XY-DF526B-44LBGDW	2X22	10.50	11.60	13.10	12.60
XY-DF526B-50LBGDW	2X25	12.00	13.10	14.60	14.10
XY-DF526B-60LBGDW	2X30	14.50	15.60	17.10	16.60
XY-DF526B-70LBGDW	2X35	17.00	18.10	19.60	19.10
XY-DF526B-80LBGDW	2X40	19.50	20.60	22.10	21.60

DIMENSION IN mm

TOLERANCE UNLESS
OTHERWISE SPECIFIED

.X±0.5 X.*±1°

.XX±0.2 .X*±

.XXX±0.1 .XX*±

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd

TITLE: 0.5 Pitch B型单槽立式BTB公座嵌芯(料号2.6)无刷片镀金

DWG NO. XY-DF526B-NLBGDW

PROJ. CUSTOMER DRAWING

SIZE A4 SCALE 1:1 SHEET 1/1 REV. A