







A		B		C		D		E	
REV.		DESCRIPTION		ECN NO.		NAME		DATE	




1



2*12*12*12*12*12*12




2

3




2*72*82*9

4




2*102*11

5




2*12


GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM. x.x x.xx x.xxx		TOL. ±0.30 ±0.25 ±0.15		TITLE: MX3.0 双排 带扣 立贴	
GENERAL ANGLE: x° x.x'		±5° ±1°		DWG. NO.: WF-0E300AXP	
UNIT: mm		SCALE: none		SHEET: 2 of 2	
		DWG. SIZE: A4		LAYER: bxconn	
				DRAWN: ELLA	
				APPROVED: WILL	









2*1




2*2




2*3




2*4




2*5




2*6




2*7




2*8





2*9



2*10



2*11



2*12

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN®	
DIM. TOL. x.x ±0.30 x.xx ±0.25 x.xxx ±0.15 GENERAL ANGLE: x.° ±5° x.x' ±1°		TITLE: MX3.0 双排 带扣 立贴						
		DWG. NO.: WF-0E300AXP			CHECKED: MAX			
		PART NO.: WF-0E300AXP			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 2 of 2	DWG. SIZE: A4	LAYER: bxconn		

