



序号	品名	材质
①	0.5 Pitch D型单槽侧插BTB母座胶芯	LCP UL94 V-0,颜色:本色
②	0.5 Pitch D型单槽侧插BTB母座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
XY-DF553D-4CJMDW	2*2	0.50	2.54	3.50	2.20
XY-DF553D-6CJMDW	2*3	1.00	3.04	4.00	2.70
XY-DF553D-8CJMDW	2*4	1.50	3.54	4.50	3.20
XY-DF553D-10CJMDW	2*5	2.00	4.04	5.00	3.70
XY-DF553D-12CJMDW	2*6	2.50	4.54	5.50	4.20
XY-DF553D-14CJMDW	2*7	3.00	5.04	6.00	4.70
XY-DF553D-16CJMDW	2*8	3.50	5.54	6.50	5.20
XY-DF553D-18CJMDW	2*9	4.00	6.04	7.00	5.70
XY-DF553D-20CJMDW	2*10	4.50	6.54	7.50	6.20
XY-DF553D-22CJMDW	2*11	5.00	7.04	8.00	6.70
XY-DF553D-24CJMDW	2*12	5.50	7.54	8.50	7.20
XY-DF553D-26CJMDW	2*13	6.00	8.04	9.00	7.70
XY-DF553D-28CJMDW	2*14	6.50	8.54	9.50	8.20
XY-DF553D-30CJMDW	2*15	7.00	9.04	10.00	8.70
XY-DF553D-32CJMDW	2*16	7.50	9.54	10.50	9.20
XY-DF553D-34CJMDW	2*17	8.00	10.04	11.00	9.70
XY-DF553D-36CJMDW	2*18	8.50	10.54	11.50	10.20
XY-DF553D-38CJMDW	2*19	9.00	11.04	12.00	10.70
XY-DF553D-40CJMDW	2*20	9.50	11.54	12.50	11.20
.....	...	...	...	...	...
XY-DF553D-80CJMDW	2*40	19.50	21.54	22.50	21.20

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 100M\Omega$ 。



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.* ± 1°	APR.	Alex	TITLE: 0.5 Pitch D型单槽侧插BTB母座胶芯(料5.3)	
.XX±0.2	.X* ±	CHK.	Jack	DWG NO. XY-DF553D-NCJMDW	
.XXX±0.1	.XX* ±	DRA.	Can	PROJ.	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1