






REV.	Q'TY	ECN. NO.	APR.	DATE

序号	品名	材质
①	0.8 Pitch B型立式 BTB等座胶芯	LCP UL94 V-0, 颜色:本色
②	0.8 Pitch B型立式 BTB等座端子	铜合金/表面镀金
③	0.8 Pitch B型立式 BTB等座胶盖	不锈钢








Part No	CKT	A	B	C
XY-DF8117B-20LBMDW	2*10	7.20	13.80	12.20
XY-DF8117B-22LBMDW	2*11	8.00	14.60	13.00
XY-DF8117B-24LBMDW	2*12	8.80	15.40	13.80
XY-DF8117B-26LBMDW	2*13	9.60	16.20	14.60
XY-DF8117B-28LBMDW	2*14	10.40	17.00	15.40
XY-DF8117B-30LBMDW	2*15	11.20	17.80	16.20
XY-DF8117B-32LBMDW	2*16	12.00	18.60	17.00
XY-DF8117B-34LBMDW	2*17	12.80	19.40	17.80
XY-DF8117B-36LBMDW	2*18	13.60	20.20	18.60
XY-DF8117B-38LBMDW	2*19	14.40	21.00	19.40
XY-DF8117B-40LBMDW	2*20	15.20	21.80	20.20
XY-DF8117B-42LBMDW	2*21	16.00	22.60	21.00
XY-DF8117B-44LBMDW	2*22	16.80	23.40	21.80
XY-DF8117B-46LBMDW	2*23	17.60	24.20	22.60
XY-DF8117B-48LBMDW	2*24	18.40	25.00	23.40
XY-DF8117B-50LBMDW	2*25	19.20	25.80	24.20
.....	...	...	...	...
XY-DF8117B-200LBMDW	2*100	79.20	85.80	84.20

DIMENSION IN mm		厦门市辛译精密电子有限公司			
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyeconn Electronics Co.,Ltd			
.X±0.5	X.*±1°	APR. Alex	TITLE: 0.8 Pitch B型BTB等座胶芯(料11.7)		
.XX±0.2	.X.*±	CHK. Jack	DWG NO. XY-DF8117B-NLBMDW		
.XXX±0.1	.XX.*±	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/1



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 100V, AC.
4. 接触电阻: ≤0.05Ω.
5. 绝缘电阻: ≥500MΩ

A B C D E F	1 2 3 4 5 6	公座 (PLUG) 母座 (SOCKET)				
						
						
						
						

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*±1*	APR. Alex	TITLE: 0.8 Pitch 母座/公座 (精11.7)		
.XX±0.2	.X*±	CHK. Jack	DWG NO. XY-DF8117B-NLBMDW		
.XXX±0.1	.XX*±	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1