




REV.	DESCRIPTION	ECN NO.	NAME	DATE



1) 材质:


- 1-1 本体:LCP 94V-0 黑色
- 1-2 端子:C2680 T=0.15mm
- 1-3 铜壳:C2680 T=0.50mm

2) 镀层:

- 2-1 端子:所有面镀镍,接点镀金(参照料号编码),焊脚镀锡 50u"MIN,盐雾测试48H无氧化生锈,锡区除外

3) 技术规格

- 3-1.额定电压:40V
- 3-2.额定电流:0.5A
- 3-3.绝缘电阻:100兆欧最小
- 3-4.接触电阻:30毫欧最大
- 3-5.操作温度:-20度到85度
- 3-6.插入力:44.1N Max
- 3-7.拔出力:9.8~39.2N;
- 3-8.耐久:10000次



3	CONTACT	19	C2680R-H	PLATED Au
2	SHELL	1	C2680R-H	PLATED NI
1	HOUSING	1	LCP	UL94V-0,Black
NO.	ITEM	Q'TY	DESCRIPTION	FINISH

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN®	
DIM. TOL. X.X: ±0.25 X.XX: ±0.15 X.XXX: ±0.10		TITLE: HDMI 19P A/F 2.1VER						
GENERAL ANGLE: X.°: ±1.5° X.X°: ±1.0° X.XX°: ±0.5°		DWG. NO.: HDMI-05A			CHECKED: MAX			
		PART NO.: HDMI-05A			DRAWN: ELLA			
		UNIT: mm			APPROVED: WILL			
		SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn			