






REV.	Q'TY	ECN. NO.	APR.	DATE



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



合高(H)	公座半高	母座半高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

序号	品名	材质
①	0.5 Pitch B型半植式BTB母座触点	LCP UL94 V-0 颜色: 米黄色
②	0.5 Pitch B型半植式BTB母座端子	铜合金/表面镀金
③	0.5 Pitch B型半植式BTB母座垫片	铜合金/表面镀镍

Part No	CKT	A	B	C	D	E
XY-DF544B-10LBMDH	2X5	2.00	3.20	4.70	6.06	4.10
XY-DF544B-12LBMDH	2X6	2.50	3.70	5.20	6.56	4.60
XY-DF544B-14LBMDH	2X7	3.00	4.20	5.70	7.06	5.10
XY-DF544B-16LBMDH	2X8	3.50	4.70	6.20	7.56	5.60
XY-DF544B-18LBMDH	2X9	4.00	5.20	6.70	8.06	6.10
XY-DF544B-20LBMDH	2X10	4.50	5.70	7.20	8.56	6.60
XY-DF544B-22LBMDH	2X11	5.00	6.20	7.70	9.06	7.10
XY-DF544B-24LBMDH	2X12	5.50	6.70	8.20	9.56	7.60
XY-DF544B-26LBMDH	2X13	6.00	7.20	8.70	10.06	8.10
XY-DF544B-28LBMDH	2X14	6.50	7.70	9.20	10.56	8.60
XY-DF544B-30LBMDH	2X15	7.00	8.20	9.70	11.06	9.10
XY-DF544B-32LBMDH	2X16	7.50	8.70	10.20	11.56	9.60
XY-DF544B-34LBMDH	2X17	8.00	9.20	10.70	12.06	10.10
XY-DF544B-36LBMDH	2X18	8.50	9.70	11.20	12.56	10.60
XY-DF544B-38LBMDH	2X19	9.00	10.20	11.70	13.06	11.10
XY-DF544B-40LBMDH	2X20	9.50	10.70	12.20	13.56	11.60
XY-DF544B-44LBMDH	2X22	10.50	11.70	13.20	14.56	12.60
XY-DF544B-50LBMDH	2X25	12.00	13.20	14.70	16.06	14.10
XY-DF544B-60LBMDH	2X30	14.50	15.70	17.20	18.56	16.60
XY-DF544B-70LBMDH	2X35	17.00	18.20	19.70	21.06	19.10
XY-DF544B-80LBMDH	2X40	19.50	20.70	22.20	23.56	21.60

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*±1°	APR. Alex	TITLE: 0.5 Pitch B型半植式BTB母座系列(标准4.4)		
.XX±0.2	.X.*±	CHK. Jack	DWG NO. XY-DF544B-NLBMDW		
.XXX±0.1	.XX.*±	DRA. Can	PROJ. CUSTOMER DRAWING		
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A