

Part No	CKT	A	B	C	D	E
XY-DF835A-8LBMDW	8	2.40	3.50	5.10	4.20	4.00
XY-DF835A-10LBMDW	10	3.20	4.30	5.90	5.00	
XY-DF835A-12LBMDW	12	4.00	5.10	6.70	5.80	
XY-DF835A-14LBMDW	14	4.80	5.90	7.50	6.60	
XY-DF835A-16LBMDW	16	5.60	6.70	8.30	7.40	
XY-DF835A-18LBMDW	18	6.40	7.50	9.10	8.20	
XY-DF835A-20LBMDW	20	7.20	8.30	9.90	9.00	
XY-DF835A-22LBMDW	22	8.00	9.10	10.70	9.80	
XY-DF835A-24LBMDW	24	8.80	9.90	11.50	10.60	8.00
XY-DF835A-26LBMDW	26	9.60	10.70	12.30	11.40	
XY-DF835A-28LBMDW	28	10.40	11.50	13.10	12.20	
XY-DF835A-30LBMDW	30	11.20	12.30	13.90	13.00	
XY-DF835A-32LBMDW	32	12.00	13.10	14.70	13.80	
XY-DF835A-34LBMDW	34	12.80	13.90	15.50	14.60	
XY-DF835A-36LBMDW	36	13.6	14.70	16.30	15.40	
XY-DF835A-38LBMDW	38	14.40	15.50	17.10	16.20	
XY-DF835A-40LBMDW	40	15.20	16.30	17.90	17.00	
XY-DF835A-44LBMDW	44	16.80	17.90	19.50	18.60	
XY-DF835A-50LBMDW	50	19.20	20.30	21.90	21.00	
XY-DF835A-60LBMDW	60	23.20	24.30	25.90	25.00	
XY-DF835A-70LBMDW	70	27.20	28.30	29.90	29.00	
XY-DF835A-80LBMDW	80	31.20	32.30	33.90	33.00	
XY-DF835A-100LBMDW	100	39.20	40.30	41.90	41.00	

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.5	X.*± 1'	APR. Alex	TITLE: 0.8 Pitch连接器BTB转接箱(料3.5)				
.XX±0.2	.X*±	CHK. Jack	DWG NO. XY-DF835A-NLBMDW				
.XXX±0.1	.XX*±	DRA. Can	PROJ. 		CUSTOMER DRAWING		
			SIZE A4	SCALE 1:1	SHEET 1 / 1	REV. A	

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围： $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压： $125\text{V}, \text{AC}$ 。
4. 接触电阻： $\leq 0.02\Omega$ 。
5. 绝缘电阻： $\geq 100\text{M}\Omega$