

A

B

C

D

E

F

A








B

C

D

E

F



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100M\Omega$ 。

序号	品名	材质	High photosynthesis height (H)	The female seat height (H1)	The male seat height (H2)	Insertion height (H3)
①	0.8 Pitch 双槽立式 BTB 公座 胶芯	PA10T UL94 V-0, 颜色: 黑色	4.0	3.0	1.0	1.9
			4.5	3.5	1.0	1.9
			5.0	3.0/4.0	2.0/1.0	1.9
②	0.8 Pitch 双槽立式 BTB 公座 端子	铜合金/表面点镀金	5.5	3.5/4.5	2.0/1.0	1.9
			6.0	4.0	2.0	1.9
			6.5	4.5	2.0	1.9
③	0.8 Pitch 双槽立式 BTB 公座 吸盘	LCP UL94 V-0, 颜色: 黑色	7.0	3.0	4.0	1.9
			7.5	3.5	4.0	1.9
			8.0	4.0	4.0	1.9
			8.5	4.5	4.0	1.9

Part No	CKT	A	B	C	D	E
XY-DF820A-8LBDW	8	2.40	3.45	5.10	4.20	4.00
XY-DF820A-10LBDW	10	3.20	4.25	5.90	5.00	
XY-DF820A-12LBDW	12	4.00	5.05	6.70	5.80	
XY-DF820A-14LBDW	14	4.80	5.85	7.50	6.60	
XY-DF820A-16LBDW	16	5.60	6.65	8.30	7.40	
XY-DF820A-18LBDW	18	6.40	7.45	9.10	8.20	
XY-DF820A-20LBDW	20	7.20	8.25	9.90	9.00	
XY-DF820A-22LBDW	22	8.00	9.05	10.70	9.80	
XY-DF820A-24LBDW	24	8.80	9.85	11.50	10.60	8.00
XY-DF820A-26LBDW	26	9.60	10.65	12.30	11.40	
XY-DF820A-28LBDW	28	10.40	11.45	13.10	12.20	
XY-DF820A-30LBDW	30	11.20	12.25	13.90	13.00	
XY-DF820A-32LBDW	32	12.00	13.05	14.70	13.80	
XY-DF820A-34LBDW	34	12.80	13.85	15.50	14.60	
XY-DF820A-36LBDW	36	13.6	14.65	16.30	15.40	
XY-DF820A-38LBDW	38	14.40	15.45	17.10	16.20	
XY-DF820A-40LBDW	40	15.20	16.25	17.90	17.00	
XY-DF820A-44LBDW	44	16.80	17.85	19.50	18.60	
XY-DF820A-50LBDW	50	19.20	20.25	21.90	21.00	
XY-DF820A-60LBDW	60	23.20	24.25	25.90	25.00	
XY-DF820A-70LBDW	70	27.20	28.25	29.90	29.00	
XY-DF820A-80LBDW	80	31.20	32.25	33.90	33.00	
XY-DF820A-100LBDW	100	39.20	40.25	41.90	41.00	

DIMENSION IN mm		TOLERANCE UNLESS OTHERWISE SPECIFIED			
.X±0.5	X.*±1°	APR.	Alex	TITLE: 0.8 Pitch 双槽立式 BTB 公座 胶芯 (单槽 1.0)	
.XX±0.2	.X.*±	CHK.	Jack	DWG NO. XY-DF820A-NLBDW	
.XXX±0.1	.XX.*±	DRA.	Can	PROJ. CUSTOMER DRAWING	
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		